

## **PVA-S**

PVA-S is our specially developed water-soluble solution for dual extrusion when you need to print with styrene-based materials. PVA-S has an excellent adherence to ABS, ABS-X, ASA-X and TPU98A. PVA-S dissolves slightly slower than regular PVA and it is advised to dissolve in lukewarm water, preferably in circulated water. PVA-S can handle higher nozzle temperatures (<250°C) without the risk of cross linking and clogging the nozzle and is therefore perfect for printing with styrene-based materials which typically print at higher temperatures.

## Material features:

- Great adhesion to styrene-based materials
- Stable at higher nozzle temperatures (<250°C)</li>
- Good dissolvability in lukewarm water
- Dissolved in water
- Performs in heated environments up to 55-60 °C
- Waste can be disposed with household effluent (\*)



PVA-S is available from stock in its natural color.





## Packaging:

PVA-S will always be supplied in a vacuum bag.

Filament specs.		
Size	Ø tolerance	Roundness
1,75mm	± 0,05mm	≥ 95%
2,85mm	± 0,10mm	≥ 95%

Material properties		
Description	Testmethod	Typical value
Specific gravity	ISO 1183	1,18 g/cc
MFI 190°C / 21,6kg	ISO 1133	58 g/10min
Printing temp.	Internal method	240±10°C

## Additional info:

Recommended temperature for heated bed is ≥60°C. Do not exceed a printing temperature of 260°C for a prolonged period. PVA-S works with most of the common adhesives. The speed at which the product dissolves in water is dependent on the volume of the printed object, the amount and the temperature of the water. Higher water temperature (up to 70°C is no problem) will accelerate the dissolution. Keep in account that the temperature of the water is based on the properties of the material that you are printing with PVA-S to avoid warping issues. PVA-S can be used on most Dual printing desktop FDM or FFF technology 3D printers.

Storage: Cool and dry (15-25°C) and away from UV light. This enhances the shelf life significantly. If you remove the spool out of the vacuum bag packaging and you do not store it in a room with low moisture content, we advise you to properly dry the material before printing to avoid any quality issue.

(\*)This material is not fully biodegradable but can be disposed of through the household drain with an excess of water.

The values presented in this publication are based on eMotion Tech's knowledge and experience and are intended for reference purposes only. While eMotion Tech has made every reasonable effort to ensure the accuracy of the information in this publication, eMotion Tech does not guarantee that it is error-free, nor does eMotion Tech make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. eMotion Tech reserves the right to make any adjustments to the information contained herein at any time without notice. eMotion Tech expressly disclaims warranties of any kind regarding the information contained herein, including, but not limited to, any warranties of merchantability or fitness of a particular purpose, use or application. eMotion Tech shall not be liable for any damage, injury or loss induced from the use of eMotion Tech's products in any application. Each user should thoroughly review this publication before selecting a product and, in view of the many factors that may affect processing and application of the product, each user should carry out their own investigations and tests and determining the safety, lawfulness, technical suitability, proprietary rights, and disposal/ recycling practices of the materials for the intended application.\*